

Precision pointer micrometer

With adjustable support

ORION[®]

Application:

For quick testing of parts from series production.

Execution:

- Adjustable tolerance marks
- Carbide measuring faces
- Movable measuring probe for lifting the anvil
- Adjustable support
- Rotating dial

Delivery:

In a case



Art. no.	31477 005
Brand	ORION
Manufacturer Part Number	31477005
Min./max. length measuring range	0-25 mm
Indicating calliper measuring range	+/- 0.04 mm
Digit increment, micrometer	0.01 mm
Digit increment, indicating calliper	0.001 mm
Micrometer error limit	0.003 mm
Indicating calliper error limit	0.001 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Measurement force	8 N
Measuring surface diameter	6.5 mm
DIN	863
Calibration Group	AN
Gross Weight	0.833 kg
Product Group	3BC

EAN

4039247582587