

Random orbital sander GEX 34-125

340 watt, 230 volt, 50 Hz - grinding plate 125 mm

BOSCH

Application:

for sanding, intermediate sanding, fine sanding and removing paint. Can be used on wood, veneer, paint and filler as well as on mineral and acrylic surfaces.

Execution:


- Speed pre-selection for adjusting the speed to different materials
- Hook-and-loop closure for fast sanding disc replacement
- Aluminium bearing flange for long service life

Advantage:

- Constant speed and high removal rate for efficient results even on demanding surfaces

Delivery:

1 x multi-hole sanding plate C470, Best for Wood + Paint K120; in box



Art. no.	70536 033
Brand	BOSCH
Manufacturer Part Number	0601372300
Model	GEX 34-125
Manufacturer Article Number	0601372300
Support-disc diameter	125 mm
Min./max. idle speed	4500-12000 rpm
Power input	340 W
Oscillating diameter	5 mm
Weight	2.1 kg
With rubber-coated handle	Yes
With electronic feedback	Yes
With overload protection	No
With speed pre-selection	Yes
With soft start	No
With restart protection	No
With dead man function	No
Gross Weight	2.850 kg
Product Group	731

EAN

4059952529035