

XT 38 INOX cutting discs

Hard, iron- and sulphur-free, type A 46 T 11 BF 1415, extra thin

RHODIUS


Application:

For cutting sheet metal, pipes, steel sections and solid material.

Advantage:

- Protection against age-related power loss thanks to HydroProtect formula.

Art. no.	76113 320
Brand	RHODIUS
Manufacturer Part Number	204621
Removal performance (points system)	●●○○
Service life (points system)	●●○○
Type	A 46 T 11 BF 1415
Washer diameter	125 mm
Washer thickness	1 mm
Bore diameter	22.23 mm
Max. rotation speed	12250 rpm
Form	Straight
Design	Hard
Number of pieces per packet	50 PCS
Material to be processed	Stainless steel
Gross Weight	0.035 kg
Product Group	6BB



EAN

4011890051597