

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



Even in White

FirestoP®

tasker® C286 Balanced Microphone Cable



A	B	C	D
---	---	---	---

CATEGORY

Balanced Microphone Cable (See Audio Catalogue)

- A:** Soft **Flame Retardant PVC** sheath. Available in different color.
Outer Diam. Ø 3,80 (±0,10) mm.
- B:** Shielding in O.F.C. red copper Spiral covering 100% +
O.F.C. Tinned copper Drain Wire.
- C:** The cores will be stranded in a pair with waste filler between conductors
and wrapped with not woven polyester based tape.
Core Insulation with a compact XLPE, colored one Red and one
Transparent. Diam. Ø 1,20 (±0,10) mm.
- D:** O.F.C. red copper formation 28x0,10 mm.
Nom. Cross section 2x0,22 mm².

MARKING

**tasker® C286 2x0,22 -24 AWG O.F.C. LOW CAPACITANCE MULTILINE AUDIO
 CABLE FirestoP® ITALY**

CUSTOM

This product is also available in **L.S.Z.H., PE, PUR**, with or
 without **Steel Armor**.

Cable Properties

Conductor Resistance	90 Ω/Km ± 5%
Capacity Core/Core	75 pF/mt
Capacity Core/Shield	160 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. B / 27.10.15
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		