

EK EKHA 130 G



Sample photo

Order symbol: EKHA 130 G
Product nbr: 2538001
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013446
EI. number:
 Finland: 3425400
 Electric No. Italy: 7501010
 Electric No. Sweden: 2538001

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	190	190	130	EKHS	Base, PC
inch:	7.5	7.5	5.1	EKH 80-G	Cover
Materials:				EKH 30-T	Cover
Material:	Polycarbonate			EKH 80-T	Cover
Base colour:	RAL 7035 -light grey			EKHVT	Mounting plate
Cover screws material:	Polyamide			EKHXT	Mounting plate isolated
Cover colour:	RAL 7035 -light grey			EKV 12	DIN-35 Mounting rail
Cover screws colour:	Grey			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Impact Resistance (EN 62262): IK08	
Temperature °C (short term):	-40 ... 120 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 250 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 746C 5"	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
EKHA	Base, PC			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
				Certificates:	
				SGS Fimko	
				Gost R	

