


## GDME LED 24 YE

Industrial Connectors:Rectangular connectors GDM-series:Type A EN 175301-803 (DIN 43650) / ISO 4400:Electronic inserts for GDME

| Product description   |  |
|-----------------------|--|
| Description           | function indicator (LED) with freewheeling diode |
| Type                  | GDME LED 24 YE                                   |
| Order No.             | 831 863-001                                      |
| Standard              | DIN EN 175 301-803-A                             |
| Construction type     | A  |
| Description of Wiring |  |
| LED color             | LED yellow                                       |
| Drawing               |  |



| Technical data           |                   |
|--------------------------|-------------------|
| Rated voltage            | UC 24 V           |
| Rated current            | 8 A               |
| Environmental conditions |                   |
| Temperature range        | -40 °C to +110 °C |
| Packaging unit           |                   |
| Packaging unit           | 50 pieces         |