

Specifications:

Insulator body:

Glass filled thermoplastic polyester, self-extinguishing, rated UL-94-V-0

Outer shell (sleeve):


Screw machined brass

Inner spring contact SC-4:

Stamped and formed Be gold plated or tin plated, accepts $\varnothing 0.40$ to 0.56 or rectangular pin 0.25 x 0.45

Order code	Size	A	B	C	No. of pins
22-1715	0.3in	10.1	10.1	7.62	08
22-1716	0.3in	10.1	10.1	7.62	14
22-1717	0.3in	20.3	10.1	7.62	16
22-1718	0.3in	20.3	10.1	7.62	18
22-1719	0.6in	35.5	17.7	15.24	28
22-0250	0.6in	50.6	17.7	15.24	40

	Standard SC-4	
Insertion/extraction per line using a $\varnothing 0.43$ test pin	Insertion	320g max.
	Extraction	50g min.



	Pin style	AA-D
	Plating sleeve (pin)	5.0 μ Sn Tin/Lead
	Plating contact (clip)	0.5 μ Au 18c flash