

Han HD shielded module female



Part number	09 14 027 3113
Specification	Han HD shielded module female
HARTING eCatalogue	https://b2b.harting.com/09140273113

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® High density shielded module

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	27
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm ²
Rated current	2 A
Rated voltage	16 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Contact resistance, shielding	≤10 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	LCP
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

	IEC 61984
--	-----------

Commercial data

Packaging size	1
Net weight	34 g
Country of origin	Germany
European customs tariff number	85389099