



IN TUNE WITH TECHNOLOGY

SINCE 1937

www.antiference.co.uk

HDMI

HDMI0102SV3 / HDMI0104SV3 / HDMI0108SV3

1 to 2 / 1 TO 4 / 1 TO 8 HDMI Splitter with 4K HDCP 2.2 & Auto Scaling



Description

- Split a single HDMI source to 2, 4 or 8 locations/screens
- 4K HDCP2.2 supported
- SKY Q compatible
- Auto-scaling function to allow a combination of HD & 4K screens to be connected
- Manual EDID management system
- 18Gbps data speed for 4K systems
- Compact metal case design
- HDR Supported

Specification

Items	Specification
Input Ports	1 x HDMI
Output Ports	2 x HDMI / 4 x HDMI / 8 x HDMI
Power Indicator LED	1 x LED
Signal Indicator LED	2 x LED / 4 x LED / 8 x LED
HDMI Version	Compatible with HDMI1.4, HDMI2.0
HDCP Version	Compatible with HDCP1.4, HDCP2.2
HDMI Resolution	480i/480p/756i/756p/720p/1080i/1080p/4Kx2K@24/25/30/60Hz
Frequency Range	25MHz~594MHz
Video From	Support 12 bit full HD video, 3D video and 4Kx2K@30/60Hz ultra HD video
Input and Output TMDS Signal	0.5 ~1.5Vp-p(TMDS)
Input and Output DDC Signal	5Vp-p(TTL)
Audio	Support standard audio and DSD (Direct Steam Digital) and HD(HBR) audio
Working Temperature	0°C - 60°C
Power Supply	DC5V/1A
Power Consumption	<5W / <5W / <20W
Dimension	96mm(L)x59mm(W)x16.8mm(H) 96mm(L)x59mm(W)x16.8mm(H) 262mm(L)x81.6m(W)x23.5mm(H)
Weight	100g
Colour	Black