


Standard Pulleys, Inch Pitch ISO 5294



Type 1F



Material: Up to a Teeth Number of 40 phosphated steel, from a Teeth Number of 44 grey cast iron GG25 (on request). Pre-bored.

Ordering Details: e.g.: Product No. 184 214 00, Pulleys, Pitch H = 1/2", 14 Teeth, Timing Belt Width 150, 2 Flanges

H 150: Pitch 1/2" = 12.7 mm for Timing Belt Width 1.50" = 38.1 mm

| Product No. | Number of teeth | Type | D _e mm | D _f mm | d mm | ND mm | b mm | L mm | B mm | Weight kg |
|-------------|-----------------|------|-------------------|-------------------|--------|-------|------|------|------|-----------|
| 184 214 00 | 14 | 1F | 55,22 | 63 | 56,60 | 40 | 46 | 58 | 18 | 0,92 |
| 184 215 00 | 15 | 1F | 59,27 | 66 | 60,64 | 45 | 46 | 58 | 18 | 1,08 |
| 184 216 00 | 16 | 1F | 63,31 | 71 | 64,68 | 45 | 46 | 58 | 18 | 1,20 |
| 184 217 00 | 17 | 1F | 67,35 | 75 | 68,72 | 45 | 46 | 58 | 18 | 1,24 |
| 184 218 00 | 18 | 1F | 71,39 | 79 | 72,77 | 55 | 46 | 58 | 18 | 1,58 |
| 184 219 00 | 19 | 1F | 75,44 | 83 | 76,81 | 60 | 46 | 58 | 18 | 1,77 |
| 184 220 00 | 20 | 1F | 79,48 | 87 | 80,85 | 62 | 46 | 58 | 18 | 1,97 |
| 184 221 00 | 21 | 1F | 83,52 | 91 | 84,89 | 65 | 46 | 58 | 18 | 2,08 |
| 184 222 00 | 22 | 1F | 87,56 | 93 | 88,94 | 68 | 46 | 58 | 18 | 2,39 |
| 184 223 00 | 23 | 1F | 91,61 | 97 | 92,98 | 72 | 46 | 58 | 18 | 2,50 |
| 184 224 00 | 24 | 1F | 95,65 | 103 | 97,02 | 72 | 46 | 58 | 18 | 2,73 |
| 184 225 00 | 25 | 1F | 99,69 | 106 | 101,06 | 72 | 46 | 58 | 18 | 3,05 |
| 184 226 00 | 26 | 1F | 103,73 | 111 | 105,11 | 80 | 46 | 58 | 18 | 3,25 |
| 184 227 00 | 27 | 1F | 107,78 | 115 | 109,15 | 80 | 46 | 58 | 18 | 3,86 |
| 184 228 00 | 28 | 1F | 111,82 | 119 | 113,18 | 80 | 46 | 58 | 18 | 3,87 |
| 184 230 00 | 30 | 1F | 119,90 | 127 | 121,28 | 80 | 46 | 58 | 18 | 4,37 |
| 184 232 00 | 32 | 1F | 127,99 | 135 | 129,36 | 80 | 46 | 58 | 18 | 4,93 |
| 184 233 00 | 33 | 1F | 132,03 | 138 | 133,40 | 80 | 46 | 58 | 18 | 5,14 |
| 184 234 00 | 34 | 1F | 136,07 | 143 | 137,45 | 80 | 46 | 58 | 18 | 5,35 |
| 184 235 00 | 35 | 1F | 140,12 | 148 | 141,49 | 80 | 46 | 58 | 18 | 5,73 |
| 184 236 00 | 36 | 1F | 144,16 | 152 | 145,53 | 80 | 46 | 58 | 18 | 6,16 |
| 184 238 00 | 38 | 1F | 152,24 | 158 | 153,62 | 80 | 46 | 58 | 18 | 6,83 |
| 184 240 00 | 40 | 1F | 160,33 | 168 | 161,70 | 80 | 46 | 58 | 18 | 7,44 |

H 200: Pitch 1/2" = 12.7 mm for Timing Belt Width 2.00" = 50.8 mm

| Product No. | Number of teeth | Type | D _e mm | D _f mm | d mm | ND mm | b mm | L mm | B mm | Weight kg |
|-------------|-----------------|------|-------------------|-------------------|--------|-------|------|------|------|-----------|
| 184 314 00 | 14 | 1F | 55,22 | 63 | 56,60 | 40 | 58,7 | 70 | 18 | 1,14 |
| 184 315 00 | 15 | 1F | 59,27 | 66 | 60,64 | 45 | 58,7 | 70 | 18 | 1,16 |
| 184 316 00 | 16 | 1F | 63,31 | 71 | 64,68 | 45 | 58,7 | 70 | 18 | 1,49 |
| 184 317 00 | 17 | 1F | 67,35 | 75 | 68,72 | 45 | 58,7 | 70 | 18 | 1,56 |
| 184 318 00 | 18 | 1F | 71,39 | 79 | 72,77 | 55 | 58,7 | 70 | 18 | 1,93 |
| 184 319 00 | 19 | 1F | 75,44 | 83 | 76,81 | 60 | 58,7 | 70 | 18 | 2,05 |
| 184 320 00 | 20 | 1F | 79,48 | 87 | 80,85 | 62 | 58,7 | 70 | 18 | 2,42 |
| 184 321 00 | 21 | 1F | 83,52 | 91 | 84,89 | 65 | 58,7 | 70 | 18 | 2,67 |
| 184 322 00 | 22 | 1F | 87,56 | 93 | 88,94 | 68 | 58,7 | 70 | 18 | 2,94 |
| 184 323 00 | 23 | 1F | 91,61 | 97 | 92,98 | 72 | 58,7 | 70 | 18 | 3,23 |
| 184 324 00 | 24 | 1F | 95,65 | 103 | 97,02 | 72 | 58,7 | 70 | 18 | 3,49 |
| 184 325 00 | 25 | 1F | 99,69 | 106 | 101,06 | 72 | 58,7 | 70 | 18 | 3,76 |
| 184 326 00 | 26 | 1F | 103,73 | 111 | 105,11 | 80 | 58,7 | 70 | 18 | 4,15 |
| 184 327 00 | 27 | 1F | 107,78 | 115 | 109,15 | 80 | 58,7 | 70 | 18 | 4,44 |
| 184 328 00 | 28 | 1F | 111,82 | 119 | 113,18 | 80 | 58,7 | 70 | 18 | 4,77 |
| 184 330 00 | 30 | 1F | 119,90 | 127 | 121,28 | 80 | 58,7 | 70 | 18 | 5,34 |
| 184 332 00 | 32 | 1F | 127,99 | 135 | 129,36 | 80 | 58,7 | 70 | 18 | 6,16 |
| 184 333 00 | 33 | 1F | 132,03 | 138 | 133,40 | 80 | 58,7 | 70 | 18 | 6,45 |
| 184 334 00 | 34 | 1F | 136,07 | 143 | 137,45 | 80 | 58,7 | 70 | 18 | 6,73 |
| 184 335 00 | 35 | 1F | 140,12 | 148 | 141,49 | 80 | 58,7 | 70 | 18 | 7,33 |
| 184 336 00 | 36 | 1F | 144,16 | 152 | 145,53 | 80 | 58,7 | 70 | 18 | 7,74 |
| 184 338 00 | 38 | 1F | 152,24 | 158 | 153,62 | 80 | 58,7 | 70 | 18 | 8,65 |
| 184 340 00 | 40 | 1F | 160,33 | 168 | 161,70 | 80 | 58,7 | 70 | 18 | 9,46 |



**Reworking within
24h-service possible.
Custom made parts
on request.**