


559/560 Series Fuse Holders for TE5/TR5 Type Fuses

RoHS




Dimensions units in mm

559 Series



560 Series



Product Characteristics

	559 Series (Lead Free)	560 Series
Compatible Fuses	TR5/TE5	TR5/TE5
Materials	Holder: Black Thermoplastic, UL94 V-0 Polyamide PA 66	Holder: Thermoplastic, UL 94 V-0 Polyester PET
	Metal Parts: Copper alloy; solderable tinned	
Electrical Data (23°C)	Rated Voltage: 250V	
	Max. Current/Power: 6.3 A /1.6 W	
Mounting	PC Board, 7.18 mm pin spacing	PC Board, 5.08 mm pin spacing
Solderability	max. 260 °C, 10 s (Wave)	
Minimum Cross Section	Conducting path - 0.1 mm ²	
Unit Weight	0.63 g	0,4 g

Note: Ensure proper fuseholder de-rating.

Ordering Information

Ordering Number	"A" Height Options	Packaging
559 0000 00 01 ²	6.5 mm (code 0001)	1000 Pcs Bulk
559 0000 80 11 ²	9.8 mm (code 8011)	1000 Pcs Bulk
560 0000 13 19 ¹	3.0 mm (code 1319)	1000 Pcs Bulk
560 0000 10 09 ¹	4.3 mm (code 1009)	500 Pcs Bulk
560 0000 10 19 ¹	4.3 mm (code 1019)	1000 Pcs Bulk

1. UL Recognized. 2. Pb free