


Gro-Lux T8 F30W/T8/GRO 0000150



Product features

- High level of blue and red radiation helps promote healthy plant growth. Enhanced the natural colours of aquatic plants and fish in aquariums. For lighting of fresh water aquariums. Recommended also for use in greenhouses and indoor gardens.



PRODUCT OVERVIEW

Product name	F30W/T8/GRO
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	SPG
ETIM Class	EC000108
E-number FI	4943112
E-number SE	8356672
Light colour	Grolux
Wattage (W)	30.00
Product Voltage (V)	96
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	14000
Product EAN number	5410288001500

DATA TABLE

General data

Product name	F30W/T8/GRO
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	SPG
Operating temperature range (°C)	-15°C...+40°C
ETIM Class	EC000108
E-number FI	4943112

Gro-Lux T8 F30W/T8/GRO 0000150

E-number SE 8356672

Optical data

Ambient temperature for maximum luminous flux (°C)	25
Light colour	Grolux
Adjustable chromaticity	N

Electrical data

Wattage (W)	30.00
Watt (Rated) - High frequency (W)	24.00
Current (A)	0.365
Product Voltage (V)	96
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	365

Lifetime data

Average life (Nominal) (h)	14000
----------------------------	-------

Physical data

Nominal Product Length (mm)	900.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	894.4
Length base to pin Min-Max (mm) - B	899.3-901.7
Max. Lamp Length (mm) - C/L	908.8
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.122

Packaging

Single packaging type	Carton
Product EAN number	5410288001500
Packaging single length / height (cm)	90.9
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288001507
Units per outer package	25
Packaging outer length / height (cm)	93.5
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

Safety data

Lamp mercury content (mg)	2.80
Optimal operating condition (°C)	-15-40
Breakage cleaning instructions	Applicable
Special purpose lamp	Yes
Intended purpose	Petcare (not including High UV content), Horticulture



Gro-Lux T8
F30W/T8/GRO
0000150

Suitable for household illumination
Safety message

No
Not suitable for household