

**MODLINK MSDD DATA INSERT**

2×USB-A female/male 0,7m cable + 1×RJ45

RJ45; USB; USB (A)

1× RJ45, 8-pole metal, CAT5e (female/female)

2× USB (female/female/0.7 m cable) form A

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85444290
GTIN	4048879037761
Packaging unit	1

**Mechanical data | Mounting data**

Height	88 mm
Width	51 mm
Depth	45 mm

**Environmental characteristics | Climatic**

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

**Shielding plate**

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque 0,9 Nm

**USB**

Operating voltage AC 48 V

Operating voltage DC 48 V

Operating voltage DC (UL-listed) 42,4 V

Operating current max. 500 mA

USB specification 2.0

Data transmission rate max. 480 MBit/s

Looking techniques Snap-in connector

**RJ45**

Operating voltage AC max. (UL-listed) 30 V

Operating voltage DC max. (UL-listed) 42,4 V

Current operating max. (UL) 175 mA

Family construction form RJ45

Family type Back side RJ45

Cable category min. Cat5e

Looking techniques Snap-in connector