

**SAK Series
AP SAKR BE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	AP SAKR BE
Order No.	0211360000
Version	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190184834
Qty.	20 pc(s).

SAK Series
AP SAKR BE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	1.5 mm	Width (inches)	0.059 inch
Height	42 mm	Height (inches)	1.654 inch
Depth	25 mm	Depth (inches)	0.984 inch
Net weight	1.7 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Version	End plate
---------	-----------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.1	27-14-11-33

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Engineering Data	STEP