

Han-Eco Cable gland M25



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 41 000 5121 |
| Specification | Han-Eco Cable gland M25 |
| HARTING eCatalogue | https://b2b.harting.com/19410005121 |

Identification

| | |
|--------------------------|-------------|
| Category | Accessories |
| Series of hoods/housings | Han-Eco® |
| Type of accessory | Cable gland |

Technical characteristics

| | |
|----------------------|-------------------------------|
| Tightening torque | 10 Nm Fitting 4 Nm Cap nut |
| Wrench size | 29 |
| Limiting temperature | -40 ... +125 °C |
| Size | M25 |
| Clamping range | 9 ... 17 mm |

Material properties

| | |
|-------------------------------------|----------------------|
| Material (cable glands) | Polyamide (PA) |
| Colour (accessories) | RAL 9005 (jet black) |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |



Pushing Performance
Since 1945

Material properties

| | |
|------------------------------------|--------------|
| Requirement set with Hazard Levels | R22 (HL 1-3) |
| | R23 (HL 1-3) |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 2 |
| Net weight | 16 g |
| Country of origin | Germany |
| European customs tariff number | 84849000 |
| GTIN | 5713140193000 |
| eCl@ss | 27140801 Screwed cable gland (electrical) |