

Torque screwdriver set TorqueVario®-S ESD



0,4-1,0 Nm assorted, variably adjustable torque limit, 14-pcs. incl. box

2882S13

Order-No.		
43898	1	
○	1 x Torque screwdriver TorqueVario®-S ESD variably adjustable torque limit	
○	1 x Bit holder clamping with ball for torque screwdriver with long handle	
	1 x Setting tool for torque screwdriver with long handle	
⊕	1 x PH0 / 1 x PH1	
⊕	1 x PZ0 / 1 x PZ1	
⊕	1 x T4 / 1 x T5 / 1 x T6 / 1 x T8	
	1 x Box	

DIN EN ISO 6789.
IEC 61340-5-1.

Torque screwdriver TorqueVario®-S ESD




variably adjustable torque limit

2882

Order-No.	Nm	±%	⊕	⊖	⊕	⊖
36851	0.04 - 0.46•	10 %	4.0	127	23	1
26865	0.1 - 0.6•	10 %	4.0	127	23	1
36852	0.1 - 0.6•	6 %	4.0	127	23	1
26629	0.4 - 1•	6 %	4.0	127	23	1
26866	0.5 - 2•	6 %	4.0	131	30	1
30495	0.8 - 5•	6 %	4.0	138	36	1

• Precision in range of 0.1-0.46 Nm.
IEC 61340-5-1. DIN EN ISO 6789.

INFOBOX:
**Electrostatic
conductive ESD tools**



- Dissipative tools by Wiha discharge the electrostatic energy in a controlled, safe manner.
- ESD tools meet the ESD Standard IEC 61340-5-1.