



Pluggable Terminal Blocks

3.5 mm Pitch, Closed Ended, vertical



Closed ended

Closed headers

Polarised mouldings

Guided pin alignment

Pin/terminal - Tinned phosphor bronze

Rising clamp - Nickel copper flash brass

Screw/torque - M2 steel Tin plated, 0.3Nm

Recommended PCB hole size $\varnothing 1.2$ mm

SPECIFICATION:

Gender of contacts	Male
Rated current to EN	10 A
Pitch	3.5 mm
Termination type	Solder Pin [PCB, Through-Hole]
Rated voltage to EN	200 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-33...+120 °C

PRODUCT RANGE:

Art. Nr.	Poles	A	Length	Connection direction
RND 205-00100	2	8.4 mm	8.4 mm	vertical
RND 205-00101	3	11.9 mm	11.9 mm	vertical
RND 205-00102	4	14 mm	14 mm	vertical
RND 205-00103	5	17.5 mm	17.5 mm	vertical
RND 205-00104	6	21 mm	21 mm	vertical
RND 205-00106	8	28 mm	28 mm	vertical
RND 205-00107	9	31.5 mm	31.5 mm	vertical