



## Notes:

### 1. Electrical characteristics



- 1.1 Contact resistance: 30mΩ max. initial.
- 1.2 Dielectric withstanding voltage: 500V AC(rms) for 1 minute
- 1.3 Insulation resistance: 1000MΩ min.

### 2. Environment characteristics

- 2.1 Operating temperature: 0°C to +85°C
- 2.2 Storage temperature; -20°C to +70°C



No.	Description	Material	Plating
1	Housing	Thermoplastic	UL 94 V-0
2	Contact	Copper Alloy	Gold Plated



SINGLE ROW  
N: Number of contacts

Number of pins	Order code
2	<b>19-0090</b>
3	<b>19-0091</b>
4	<b>19-0092</b>
5	<b>19-0093</b>
10	<b>19-0094</b>
15	<b>19-0095</b>
16	<b>19-0096</b>
20	<b>19-0097</b>
25	<b>19-0098</b>