


AC5031



Lower part for AS-Interface module

EMS-BASE RC ST SET



1 locking bolt

Electrical data

Operating voltage [V] 26.5...31.6 DC

Outputs

Electrical design AS-i
Contact rating < 4 A

Operating conditions

Ambient temperature [°C] -25...85
Protection IP 65

Mechanical data

Weight [g] 115.2
Type of mounting mounting on DIN rail and panel
Materials PBT

Accessories

Accessories (supplied)
flat cable seals: 2, NBR
cable glands: 3
Protective caps: 3
hexagon nuts: 4

Accessories (optional)
cover, for AS-i module, AC3000
screw terminal insert, AC5007

Remarks

Remarks up to 4 M20 cable ports for any T and cross branches
Pack quantity 1 pcs.

AC5031



Lower part for AS-Interface module

EMS-BASE RC ST SET

Electrical connection

screw terminals: ...2.5 mm²