

## PCV24150 – Non IP Rated Constant Voltage Power Supply



PCV24150 is a 24VDC, 6.25A Constant Voltage LED Lighting Power Supply suitable for indoor applications. PCV24150 has 100 ~240VAC input voltage and features captive terminal screws and a snap lock cable strain for easy installation.

SKU: PCV24150

Category: LED DRIVERS



PCV24150 is a 24VDC, 6.25A Constant Voltage LED Lighting Power Supply suitable for indoor applications. PCV24150 has 100 ~240VAC input voltage featuring captive terminal screws and a snap lock cable strain for easy installation. PCV24150 is of a class II design and includes an over load, short circuit and thermal protection

### Additional information

Weight	0.40 kg
Product Type	AC/DC, Constant Voltage, LED Driver
Functions	Latch Off
Outputs	Single
Dimensions	216 x 74 x 42mm
Input Voltage	100 ~ 240VAC
IP Rating	IP20
Output Current	0-6.25A
Output Voltage	24VDC
Power	150W
tape-length	216
Efficiency	87%
Connections	Screw Terminal on I/P & O/P
Weight	750g
Dimensions	216 x 74 x 42mm

### Features

- Captive terminal screws for ease
- Snap lock cable strain relief
- LED indicator for power on
- Over load, short circuit and thermal protection
- Class II product
- Safe no load operation
- Suitable for indoor lighting applications
- Superior latch off protection
- Energy Efficient and Energy compliant