

Han 24B cover plastic/DL/HBM, HSM, HCC



Part number	09 30 024 5405
Specification	Han 24B cover plastic/DL/HBM, HSM, HCC
HARTING eCatalogue	https://b2b.harting.com/09300245405

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings Thermoplastic

Version

Size	24 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals DNV GL	
------------------	--

Commercial data

1
24 g
Germany
85389099
5713140047921
EC002314
27440208 Cap for industrial connectors