

## HSSE PM roughing cutter

5 cutters, TiAlN-coated

**ORION**<sup>®</sup>

### Application:

Roughing cutter for universal machining in a wide range of materials.

### Execution:

- HSSE PM
- TiAlN-coating for maximum service life
- Straight shank according to DIN 1835 B
- Type NR
- Roughing teeth



|                                       |                   |
|---------------------------------------|-------------------|
| <b>Art. no.</b>                       | <b>15905 120</b>  |
| <b>Brand</b>                          | ORION             |
| <b>Manufacturer Part Number</b>       | 15905 120         |
| <b>Cutting material</b>               | HSSE-PM           |
| <b>Surface</b>                        | TiAlN             |
| <b>Type</b>                           | NR                |
| <b>Number of cutting edges</b>        | 5 PCS             |
| <b>Twist angle</b>                    | 30°               |
| <b>Edge protection chamfer length</b> | 0.2 mm            |
| <b>Tool holding device</b>            | HB parallel shank |
| <b>Construction length</b>            | Normal            |
| <b>Cutting edge diameter</b>          | 12 mm             |
| <b>Cutting edge length</b>            | 26 mm             |
| <b>Length</b>                         | 83 mm             |
| <b>Shank diameter</b>                 | 12 mm             |
| <b>fz steel 700</b>                   | 0.09 mm           |
| <b>Gross Weight</b>                   | 0.071 kg          |
| <b>Product Group</b>                  | 106               |

### EAN

4039247598823