

## Electronic 3-point internal micrometers set IP65

Mitutoyo

### Application:

For measuring through-bores and for blind holes and short centring shoulders.

### Execution:

- Titanium-coated carbide (6–12 mm)
- Titanium-coated hardened steel (12–100 mm)
- LCD display, digit size 7.5 mm
- Automatic switch-off after 20 min. Non-use
- ABS function
- HOLD function
- Preset function
- Digimatic
- IP65
- Friction coupling for consistent, repeatable measuring force

### Advantage:

- suitable for present use of coolants or cutting oils

### Delivery:

Includes box, adjustment wrench, SR-44 battery, setting ring



<b>Art. no.</b>	<b>32017 679</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	468-981
<b>Min./max. length measuring range</b>	6-12 mm
<b>Data transmission type</b>	DIGIMATIC
<b>Digit increment</b>	0.001 mm
<b>IP protection class</b>	IP 65
<b>Number of measurement heads</b>	3 PCS
<b>Adjusting ring diameter</b>	8 mm, 10 mm
<b>Preset function</b>	Yes
<b>With ABS function</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	3 PCS
<b>Battery designation</b>	1,5 V SR44
<b>Calibration Group</b>	I
<b>Gross Weight</b>	1.815 kg
<b>Product Group</b>	3MA

### EAN

4946368562919