

electronic pocket vernier calipers

Digital ABS AOS vernier caliper

Mitutoyo

Application:

For measuring external, internal, step and depth dimensions.

Execution:

- ON/OFF
- Zero setting at any position
- ORIGIN
- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- AOS (advanced on-site sensor) magnetic-inductive scale
- No influence on the measurement due to contamination of the scale (dust, oil, water etc.).
- Smooth and stable guide surfaces

Delivery:

Delivered in box



Art. no.	32018 023
Brand	MITUTOYO
Manufacturer Part Number	500-184-30
Min./max. length measuring range	0-150 mm
Data transmission type	No
Depth gauge rod	Round
With drive wheel	No
Error limit	0.02 mm
Length of jaw	40 mm
Design	Metric
Digit height	9 mm
Length of cross tips	16.5 mm
Digit increment	0.01 mm
Depth gauge rod thickness	1.9 mm
Type of locating	With locking screw
Preset function	No
With mm / inch switching	No
Length	233 mm
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	ABS function, Absolute function, Origin (Dimension preset), On/Off
Gross Weight	0.429 kg
Product Group	3MA

EAN

4946368667775