

Compact manual hydraulic punch with overpressure valve

Angled 90°



Application:

For punching holes with Tristar sheet metal punches.

Execution:

- Aluminium version
- Weighs just 1.9 kg
- 75 kN punching force
- Max. operating pressure: 650 bar
- Punching capacity: Round holes up to 82 mm/2 mm sheet metal, 64 mm/3 mm sheet metal
- Square hole punch up to 68 x 68 mm/2 mm sheet metal
- Square hole punch up to 46 x 86 mm/2 mm sheet metal
- Set comprising hydraulic punch, 19 and 19 x 9.5 mm tension bolt, HSS 11.0 mm drill for pre-drilling, 3-piece spacer sleeve set
- Set in robust and practical plastic case

Advantage:

- Tool service life is extended by the integrated overpressure valve with automatic pressure shutdown at 650 bar
- With 90° angled and 360° rotating cylinder head, making it ideally suited to confined spaces
- Easy to position the stencils on the crosshairs thanks to one-handed operation



Art. no.	53829 210
Brand	ALFRA
Manufacturer Part Number	02050
Design	Offset
Suitable for max. sheet metal thickness	3 mm
Gross Weight	3.700 kg
Product Group	554

EAN

4030266008348