

NOTES:

ELECTRICAL:


1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5AMP
3. CONTACT RESISTANCE: 100MILLIOHMS MAX
4. INSULATION RESISTANCE: 100 MEGOHMS MIN @500 VDC
5. DIELECTRIC STRENGTH: 750 VAC RMS 60Hz, 1MIN

ENVIRONMENTAL:

1. STORAGE: -40°TO+85°
2. OPERATION: 0°TO70°


MECHANICAL:

1. HOUSING MATERIAL: PC
2. INSERT MATERIAL: FAME RETARDANCY ABS
3. PCB MATERIAL: FR-4 T=1.6mm
4. CONTACT MATERIAL: PHOSPHOR BRONZE  
STAMP PIN T=0.30mm
5. IDC CONTACT MATERIAL: PHOSPHOR BRONZE T=0.50mm WITH TIN PLATING



镀铬

75001



1	CONNECTORS	CAT 6 LSA CONNECTION BOX 250 MHz
2	MOLDING	
3	CABLE	PLASTIC HOUSING, METALLIZED
NO	PART NAME	

shiverpeaks®

DESCRIPTION

CAT 6 LSA CONNECTION BOX

SIZE	A4	DATE		CHECKED		TOL	BS75001
UNIT	MM	DRAWN		APPROVED			
CUSTOM TARIF NO.: 85369010000							