



### **LC8074: Classic Round Magnifier Lamp with Sun Cap**

#### **Features & Benefits:**

- Electronic ballast - more energy efficient
- 22 watt circular energy saving tube (LC8064/T)
- Shadow free light with low heat emission
- Quality 125mm (5") handle for easy positioning
- Inbuilt sun protector cap
- Includes table clamp with cone holder for extra stability
- Cable length 1.5m

**Specifications:** A classic round 22w daylight lamp with round glass lens & quick positioning handle, ideal for close-up and intricate work. Includes Pro-Joints for extra flexibility & positioning.

### **LC8076: Long Reach Slim Line Magnifier Lamp**

#### **Features & Benefits:**

- Electronic ballast - more energy efficient
- 16 watt energy saving fluorescent tube (LC8076/T)
- Shadow free light with low heat emission
- Quality 125mm (5") lens, 3 dioptr (1.75x mag.)
- Removable sun protector cap
- Includes table clamp with cone holder for extra stability
- Cable length 1.5m

**Specifications:** A round 16w daylight lamp with glass lens, featuring longer arms with sturdy joints for extra flexibility & positioning. Ideal for close-up intricate work.

### **LC8076/T: Spare Tube for LC8076**

#### **Features & Benefits:**

- 16 watt energy saving fluorescent tube
- Replacement tube for LC8076

**Specifications:** Energy saving fluorescent daylight tube providing a consistent shadow free light source (**6400K**), with low heat emission - ideal for longer, comfortable use.

### **LC8079: Rectangular Long Reach Magnifier Lamp**

Fluorescent daylight Rectangular Long Reach Magnifier Lamp-A robust daylight lamp with high quality wide glass lens for close-up & intricate work. Includes Pro-Joints for professional and hobby use.

#### **Features & Benefits**

- Electronic ballast – more energy efficient
- 1 x 28 watt circular energy saving tube
- Shadow free light with low heat emission
- Quality 190 x 160mm (7.5 x 6.2”) lens, 3 dioptre (1.75x mag.)
- Inbuilt sun protector cap
- Includes table clamp with cone for extra stability

#### **Specifications:**

Voltages available: 220v – 240v, 50hz

Magnifier: 190 x 160mm (7.5 x 6.2”); 3 dioptre lens

Magnification: 1.75x mag.

Tube type: 1 x 28 w circular fluorescent (LC8079/T)

Tube protection cover: yes

Cable length: 1.5m

Table fixing: adjustable clamp with cone stabiliser

### **LC8079T: Spare Tube for LC8079**

#### **Features & benefits:**

- 1 x 28 watt circular energy saving tube

#### **Specifications:**

Tube type: 1 x 28 w circular fluorescent (LC8079/T) and tube protection cover.

### **LC1850: Dual Purpose Neck & Desk Magnifier**

#### **Features & benefits:**

- Quality 10mm/4" Lens with 2x magnification
- Inbuilt mini lens with close-up 6x magnification
- Twin bulb LED light
- Dual purpose hands free neck magnifier with adjustable cord and table stand (Requires 3x AAA batteries - Not included)

**Specifications:** Dual Purpose Neck & Desk Magnifier with Twin Bulb LED Light. Ideal for close-up precision work leaving your hands free, including craft, sewing, reading, hobby or small repair projects.

## **LC1890: Handheld Magnifier**

### **Features & benefits:**

- Magnification 2.5x
- Lens dimensions 90mm diameter
- 2 white LED bulbs
- soft grip body - comfortable grip
- Inbuilt rest for placing safely on desk
- 3 x LR batteries fitted - remove pull tab to activate
- To replace batteries, simply unscrew the battery compartment

**Specifications:** Ideal for close-up work with twin bulb LED light and inbuilt rest. Perfect for model making, craft work, electronics, renovation, jewellery, small DIY tasks, sewing, reading, artwork and household repairs.

## **LC1770: 5 Lens Magnifier Set**

### **Features & benefits:**

- Magnification 2.5x
- Lens dimensions 90mm diameter
- 2 white LED bulbs
- Comfortable, lightweight frame
- 5 precision interchangeable lenses; covering all focal lengths from semi close-up to very close-up
- Lens & LED light angles can be adjusted
- Quick change lenses simply clip into slot on LED light head - lens should be angled to clip into position
- Lens storage case
- Fitted with 3 x LR1130 batteries - simply remove pull tab to activate

### **Specifications:**

Magnification	Working Distance mm/inches
1.0x	250-350mm (10-14")
1.5x	200-300mm (8-12")
2.0x	175-275mm (7-11")
2.5x	125-250mm (5-10")
3.5x	75-125mm (3-5")

## **LC8093LED Professional LED Task Lamp with Dimmer Feature**

An energy efficient LED daylight lamp with glass lens & versatile swivel head, ideal for intricate work.

### **Features & benefits:**

- 30 white LED bulbs, only in 2w in total
- Energy efficient
- Bulbs never need replacing
- Shadow free, cool light
- Quality 100mm (4") glass lens 3 dioptre (1.75 x magnification)
- Built-in close up lens 12 dioptre ( 4 x magnification)
- Ergonomic design with table base & lens cap
- Quality arm ball joints for easy positioning

### **Specifications:**

Voltages available: 220v – 240v, 50hz

Magnifier: 100mm (4") diameter, 3 dioptre lens with 120 mini lens

Magnification: 1.75x and 4x for mini lens

Sun protector cap: Yes

Light specification: 30 LEDs (2w)

Tube protector cover: Yes

Cable length: 1.5m

Table base: integral

Arm adjustment

Small tool included in base

Suitable for UK and EU countries

Ideal for: Airbrushing, Clock & Watchmaking, Fly Tying, Art & Graphics, Computer Repair, Jewellery Archaeology, Crafts, Modelling, Automotive, DIY, Nail Painting, Beauty, Dental Laboratories, Optical Repairs, Bonsai, Cake decorating, Camera Repair ,Carving, Ceramics, Chiropody, Electronics ,Engraving Reading, Sculpture, Sewing ,Stamp Collecting, Wood Turning ,Dolls Houses and Miniatures

## **LC8015LED Professional LED Task Lamp**

A professional long reach lamp perfect for lighting up larger work spaces, with the flexibility of an inbuilt dimmer feature.

### **Features & benefits:**

- 84 white LED bulb, only 21w in total
- Perfect for lighting up larger work spaces
- Bulbs never need replacing
- Multi-Function dimmer switch for complete lighting versatility
- Includes table clamp and inbuilt dimmer feature
- Ergonomic design and easily positioned to suit
- Sturdy joints for simple positioning

### **Specifications:**

Adaptor plug included: UK, EU, US, AUS  
Voltages available: 120v – 240v, 50 -60Hz  
Output voltage: 24v  
Light specification: 84 LEDs (21w)  
Cable length: 1.8m  
Table clamp: included

Ideal for: Airbrushing, Clock & Watchmaking, Fly Tying, Art & Graphics, Computer Repair, Jewellery  
Archaeology, Crafts, Modelling, Automotive, DIY, Nail Painting, Beauty, Dental Laboratories, Optical  
Repairs, Bonsai, Cake decorating, Camera Repair ,Carving, Ceramics, Chiropody, Electronics  
,Engraving Reading, Sculpture, Sewing ,Stamp Collecting, Wood Turning ,Dolls Houses and  
Miniatures