

Tragfähigkeit: 200 kg  
Carrying capacity: 200 kg  
Charge utile : 200 kg



## Transportwagen/Plattformwagen



- Chromnickelstahl
- Tragfähigkeit: 200 kg
- Transportfläche: B 560 x T 940 mm
- 2 feste Rollen, 2 Lenkrollen, Ø 125 mm
- Maße: B 560 x T 1050 x H 925 mm

GTIN 4015613523705  
Art.-Nr. 300142

## Trolley / Platform trolley



- Chrome nickel steel
- Carrying capacity: 200 kg
- Platform size: W 560 x D 940 mm
- 2 fixed castors, 2 swivel castors, Ø 125 mm
- Size: W 560 x D 1050 x H 925 mm

GTIN 4015613523705  
Code-No. 300142

## Chariot de transport / Plateau du chariot



- Acier inoxydable
- Charge utile : 200 kg
- Dimension plateau : L 560 x P 940 mm
- 2 roues fixes, 2 roues dirigeables, Ø 125 mm
- Dimensions : L 560 x P 1050 x H 925 mm

GTIN 4015613523705  
Code-No. 300142