

CAB CAB PC 302018 T



Sample photo

Order symbol: CAB PC 302018 T
Product nbr: 8113030
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020017
EI. number:
 Finland: 3424151
 Electric No. 8212020210
 Denmark:
 Electric No. Italy: 7822015
 Electric No. Sweden: 2539935

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:
mm:	300	200	180	EKIV 17 DIN-35 Mounting rail
inch:	11.8	7.9	7.1	DS35170E1 DIN-35 Mounting rail

Materials:	Accessories:
Material: Polycarbonate	EKIV 27 DIN-35 Mounting rail
Base colour: RAL 7035 -light grey	DS35270E1 DIN-35 Mounting rail
Cover colour: Smoked grey	FP A 23 Swing-out door/Front plate
Gasket material: Polyurethane	MB 12225 AL Swing door set
	FP 23 Front plate
	FP 12-23 Front plate
	DRF 23 DIN rail frame set

Temperatures:	Rating:
Temperature °C (short term): -40 ... 120 °C	Ingress Protection (EN 60529): IP65
Temperature °C (continuous): -40 ... 80 °C	Impact Resistance (EN 62262): IK08
Temperature °F (short term): -40 ... 250 °F	Electrical insulation: Totally insulated
Temperature °F (continuous): -40 ... 175 °F	Halogen free (DIN/VDE 0472, Part 815): 1
	UV resistance: UL 508
	Flammability Rating: UL 746C 5"
	Glow Wire Test (IEC 695-2-1) °C: 960

Accessories:
EKIV 23 Mounting plate

Certificates:
 Germanischer Lloyd (GL)
 SGS Fimko
 Lloyds Register of Shipping (LR)
 Gost R

