

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191540028**
Status: **Active**
Overview: Splices
Description: InsulKrimp Butt Splice for 10-12 AWG Wire

Documents:

Drawing (PDF)	Product Specification PS-19902-011-001 (PDF)
Product Specification 194130096-000 (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification 194130104-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-007-001 (PDF)	

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	<u>19154</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>Splices</u>
Product Name	Butt, InsulKrimp
UPC	800753108936

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Insulation	PVC
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	2.531/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C
Wire Insulation Diameter	6.35mm max.
Wire Size AWG	10, 12
Wire Size mm ²	3.30-5.00

Electrical

Voltage - Maximum	600V
-------------------	------

Solder Process Data


Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Engineering Number	C-246X
--------------------	--------

Reference - Drawing Numbers

Product Specification	194130096-000, 194130104-000, PS-19902-007-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19154-006



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19154 Series](#)