

1303W

Indubox



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.

Protection class	IP65
Glow wire test	650 °C
Temp. range min	-5 °C
Temp. range max	85 °C
Material	Polystyrene, Polycarbonate
Product Color	RAL 7035
External dimensions LxWxH	85x155x100mm
No. Elements	3
Type	1303W
Order no. UK	1303/W
Packing unit	1

Advice:

Outer: Polystyrene, Window: Polycarbonate halogen-free,
 UV-resistant, module blanking plate, caps for external screws,
 caps for keeping class II, INOX fast screws

06.08.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk