

FEATURES

- Metric threaded
- Completely sealed against dust
- Excellent water resistance
- Made with high quality Nylon 66
- Black and white versions available

RS PRO M20 Cable Gland with Locknut, Nylon, IP68

RS Stock No.: 669-4673



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Brought to you by RS PRO, a range of metric threaded cable glands offering excellent strain relief and cable protection. Cable glands allow you to mount a cable into a pre-drilled hole. Commonly used within construction and by electrical engineers, cable glands are simple and easy to use. Each gland is rated as IP68, ensuring the level of cable protection is incredibly resilient to the outdoors and other harsh environments. All models are highly reliable and excellent quality.

General Specifications

Thread Size	M20
Material	Nylon 66
Colour	Black
Locknut Included	Yes
Application	Machinery with delicate internals, Telecommunications, Flow meters, Underwater power generators

Mechanical Specifications

Maximum Cable Diameter	14mm
Minimum Cable Diameter	10mm
Thread Length L2	28.5mm
Seals B1	14mm
Protrusion Length L1	15mm
Nut L3	18.5mm
Thread inner diameter D2	15mm
Thread outer diameter D1	20mm

Operation Environment Specifications


Minimum Operating Temperature	-60°C
Maximum Operating Temperature	85°C
Operating Temperature Range	-60°C to +85°C

Protection Category

IP Rating	IP68
-----------	------

Approvals

Compliance/Certifications	EN 61340
Standards Met	UL 94 V-2





RS Article	Thread	Mounting Hole D1	D2	B1	L1	L2	L3	Cable Range
6694679	M20xP1.5	20.0	15.0	14.0	15.0	28.5	18.5	10 ~ 14