

Coaxial Cable Connector 11_SMA-50-4-53/139_N

Description

Straight cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0071 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

Related Documents

Outline drawing	DOU-00006903
Assembly instruction	DOC-0000179057

Ordering Information

Single package	11_SMA-50-4-53/139_NE
----------------	-----------------------

Additional Information

Suitable cables	S_04272_B, S_04262B-01
-----------------	------------------------

Remarks

Use torque wrench 74_Z-0-0-79 (0.45Nm)