



Rewireable Miniature USB Plug 4-pin Male: A Type







Order code: **24-0358**

Specifications:

Current rating: 0.5A/pin max.
Voltage rating: 30V (DC)
Dielectric withstanding voltage: 100VAC 1 minute
Contact resistance: 50mΩ max.
Insulation resistance: 100MΩ min.
Temperature range: -55°C to +105°C






Materials:

Shell: Steel
Contact: gold



Hood

Housing with contact



Upper shell

Down shell