




Dimensions



Model Number

ICZ-2T/TR-0,2M-PUR ABG-V15B-G

Terminal cable for PROFIBUS with terminal resistor

Features

- Labelling cover
- Screen put on the slotted nut and Pin 5
- Data transmission up to 12 MBaud

Technical data

General specifications

Number of poles	2 + 1 x screen
Transfer rate	max. 12 MBit/s

Ambient conditions

Ambient temperature	-40 ... 85 °C (233 ... 358 K)
---------------------	-------------------------------

Mechanical specifications

Protection degree	IP65
Connection	M12 connector/socket, 4-pin, B-coded for PROFIBUS

Material

Contacts	CuZn, gold-plated
Handle	PUR / PA 66
Cable	PUR
Slotted nut	CuZn, nickel-plated

Cable

Sheath diameter	Ø 8 mm
Colour	violet
Cores	2 x 0.64 mm ²
Length	L approx. 28 cm
Mass	approx. 90 g

Electrical connection

