



BELL TRANSFORMER, 8VA PRIM 230-240V AC,50HZ, SEK 8V,12V AC WITH PTC PROT.,2MW

Figure similar

Model		
product brand name		SENTRON
Design of the transformer		Standard bell transformer
General technical data		
Active power supplied / maximum	W	8
Voltage		
Output voltage		
• _1 / Rated value	V	8
• _2 / Rated value	V	12
Dissipation		
Active power loss		
• maximum	W	5.7
Electricity		
Output current		
• maximum	A	1
• _1 / Rated value	A	1
• _2 / Rated value	A	0.6
Suitability		
Suitability for integration		
• surface-mounted installation		No
• flush mounting		No
Product details		

Product component / switch		No
----------------------------	--	----

Product function

Product function / Thermal protection		Yes
---------------------------------------	--	-----

Inputs Outputs

Property of the output / Short-circuit proof		Yes
--	--	-----

Mechanical Design

Height	mm	64
Width	mm	36
Length	mm	90
Number of width units		2
Mounting type / Side-by-side mounting		Yes

General Product Approval	Declaration of Conformity
---------------------------------	----------------------------------



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/4AC32081>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/4AC32081/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4AC32081

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015