

## BLINDNIETE



SENKKOPF MIT GERILLTEM NIETDORN (~ DIN EN ISO 15984)

## BLIND RIVETS

COUNTERSUNK HEAD WITH GROOVED MANDREL (~ DIN EN ISO 15984)

## RIVETS AVEUGLES

AVEUGLES TÊTE FRAISÉE AVEC CLOU CANNELÉ (~ DIN EN ISO 15984)



Edelstahl A2 [ 1.4301 ]  
Stainless steel A2 [ AISI 304 ]  
Acier inox A2 [ 1.4301 ]

Edelstahl A2 [ 1.4301 ]  
Stainless steel A2 [ AISI 304 ]  
Acier inox A2 [ 1.4301 ]

### Ø 5,0 mm

D1 = 5,0 + 0,08 / - 0,15 mm

D2 = 9,0 + 0 / - 0,5 mm







k = -

d = 3,0 mm

P = ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

 5,1 mm

	F-Max		CODE				
5,0 x 8,0 mm	13,4 mm	1,5 - 4,0 mm	70351 50800	5000 N	6500 N	500	5000
5,0 x 10,0 mm	15,4 mm	4,0 - 6,0 mm	70351 50100			500	5000
5,0 x 12,0 mm	17,4 mm	5,0 - 7,0 mm	70351 50120			500	5000
5,0 x 14,0 mm	19,4 mm	7,0 - 9,0 mm	70351 50140			500	5000
5,0 x 16,0 mm	21,4 mm	9,0 - 11,0 mm	70351 50160			500	5000
5,0 x 18,0 mm	23,4 mm	11,0 - 13,0 mm	70351 50180			500	5000
5,0 x 20,0 mm	25,4 mm	13,0 - 15,0 mm	70351 50200			500	5000
5,0 x 25,0 mm	30,4 mm	15,0 - 20,0 mm	70351 50250			500	5000