

PRODUCT-DETAILS

PAFS34/BL/25M

STD WGT BLK FINE NYL COND NC34 25M



General Information

Extended Product Type	PAFS34/BL/25M
Product ID	7TCA296000R2248
EAN	5020963001260
Catalog Description	STD WGT BLK FINE NYL COND NC34 25M
Long Description	Standard Weight Conduit, Nominal Conduit Size 34mm, NW Conduit Size 29, Fine Conduit Pitch, Outside Diameter 34.5mm, Inside Diameter 28.8mm, Static Bend Radius 60mm, Reel Length 25 Meters, Polyamide (Nylon) 6, Black

Ordering

EAN	5020963001260
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	7.44 lb 3.374 kg
--------------------	---------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	37 in 940 mm

Package Level 1 Height	17 in 432 mm
Package Level 1 Depth / Length	17 in 432 mm
Package Level 2 Units	1 piece
Package Level 2 Width	37 in 940 mm
Package Level 2 Height	17 in 432 mm
Package Level 2 Depth / Length	17 in 432 mm

Additional Information

Application	Indoors / Outdoors - Light Industrial, Buildings & Machinery
Brand / Label	Adaptaflex
Color	Black
Flexibility	High
Inside Diameter	28.8 mm
Material	Polyamide/Nylon 6
Nominal Size	34 mm
Number of Batteries	0
Outside Diameter	34.5 mm
Product Name	"flexible conduit, nylon"
Product Type	Standard Weight Conduit with Fine Pitch
Radius	60 mm
Special Functions	High Fatigue Life, Self Extinguishing, Halogen Free
UPC	786210147154

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	PAFS34/BL/25M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	PAFS34/BL/25M

Classifications

ETIM 6	EC001175 - Corrugated plastic hose
ETIM 7	EC001175 - Corrugated plastic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

