

TBN 10

TBN Breaking torque wrench CP

0.4-10 N · m / fixed setting

| | |
|--------------------|---------------------------------|
| Code | ETIM |
| 2905299 | ECO02132 Drehmomentschlüssel |
| EAN | UNSPSC |
| 0611702890617 | 27-11-17-15 Drehmomentschlüssel |
| Country of Origin | eCl@ss |
| England | 21-04-02-22 Drehmomentschlüssel |
| Customs tariff no. | |
| 82041100 | |



Article description

- Controlled screw tightening in the most common range of 1 - 10 N·m
- Compact slimline design. This maximises productivity in restricted space applications
- Compatible End Fittings. A range of interchangeable end fittings is available, making this an extremely versatile tool.
- Direct fastening of the insert in the key through the CP interior mount, reduces the overall length
- For bi-directional tightening (the wrench only has to be turned by 180°!)
- Breaking of the handgrip by 20° when the pre-set torque value is achieved makes over-tightening unlikely
- Lightweight, but robust and corrosion-resistant construction design

Article information

| | | | |
|------------------------------|---------|-------------------------|------------------------|
| Contents (Qty of pieces) | 1 tlg. | Trigger mechanism | Long travel triggering |
| Total length [mm] | 133 mm | Precision +/- | +/- 6 % |
| Torque (min.) [N·m] | 2 N·m | Direction of tightening | Left and right |
| Torque (max.) [N·m] | 10 N·m | Fixed setting | 1 |
| Net weight [kg] | 0,15 kg | Torque (max.) [lbf·in] | 17,8 lbf·in |
| REACH registration available | 0 | Torque (min.) [lbf·in] | 89 lbf·in |
| Epa-/Esd-Model | 1 | | |