

PRODUCT-DETAILS

T5D 630 3p F F

T5D 630 3p F F



General Information

Extended Product Type	T5D 630 3p F F
Product ID	1SDA054601R1
EAN	8015644556990
Catalog Description	T5D 630 3p F F
Long Description	SWITCH-DISCONNECTOR TMAX T5D 630 FIXED THREE-POLE WITH FRONT TERMINALS

Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
Toxic Substances Control Act - TSCA	9AKK108467A8326

Environmental

Environmental Information	9AKK10103A1056 9AKK108467A6707
REACH Declaration	9AKK108466A1425
RoHS Information	9AKK108466A1424
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	1fdc593c-e498-4bfe-afc0-e0ed9c1122af Italy (IT)
Simplified SCIP	b165941e-51ab-4239-9fc5-ee48f0c9fae4 Poland (PL)

3a5a5b6a-5983-4da6-8b69-eaf0947dc165 Germany (DE)
 e87f90ee-d4cb-40a2-9528-2500796ada6c Norway (NO)
 4259d9a1-1aae-4ee0-b0c5-7cda50e4e643 Finland (FI)
 548eebc7-f802-4941-a5ca-030463fdade Denmark (DK)
 48244e27-964d-42d8-bea3-4cb32325bd3f Greece (GR)
 4db5401f-03a1-4259-8366-4638e79ef561 Bulgaria (BG)
 84e42664-daf9-4cb7-aaf2-0dc73e564183 Netherlands (NL)
 6a96e2e0-9629-4727-bdcf-28562b26683f Germany (DE)
 e3e7e710-2be2-4971-a794-f0159820c05a Germany (DE)
 0b44202b-b1ae-4dc3-8b9b-7dcb4a413ab8 Croatia (HR)
 d6dae9c3-7eed-437b-ad5c-6274ade8f77d Czech Republic (CZ)
 a17f0b1f-80ba-4793-8b81-2398539189aa Poland (PL)
 23009673-c4b0-459d-a9ad-f89336ebb7e4 Netherlands (NL)
 0e11b245-e027-492e-afaf-2177ba2d02fb Netherlands (NL)
 dce2cc52-def2-436d-af6f-3712fd8f539a Estonia (EE)
 de84e64e-1633-4bf0-a0de-42938fd5b505 Portugal (PT)
 2465f06c-973e-4f43-bf9d-43314b76825b Sweden (SE)
 51dab352-11d8-4ab0-9049-624a6e8fc96e Poland (PL)
 36bcc96b-1ad4-4158-bc73-61101d037450 France (FR)
 66b8db6d-5a1e-44bf-8907-e468389d718c Sweden (SE)
 14388075-4bcd-43e2-8d01-737c41cd450b Germany (DE)
 c9c11825-054b-44db-a623-4fea3b191a5c France (FR)
 381ff290-0419-42f8-9b4f-b980a619f420 Netherlands (NL)
 1aec8987-71c4-43bb-bbf1-c1e36e7f6147 Spain (ES)
 0d02963b-0754-418e-a2ca-47cdb7e656ee Netherlands (NL)

Ordering

E-Number (Finland)	3655615
EAN	8015644556990
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	140 mm
Product Net Height	205 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	3.25 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	248 mm
Package Level 1 Height	240 mm
Package Level 1 Depth / Length	285 mm
Package Level 1 Gross Weight	4.585 kg
Package Level 1 EAN	8015644556990

Additional Information

Mechanical Durability	20000 cycle 120 cycles per hour
Number of Poles	3
Power Loss	at Rated Operating Conditions per Pole 41 W
Product Main Type	SACE Tmax T
Product Name	Moulded Case Circuit Breaker
Product Type	Switch Disconnecter

Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	690 V AC 750 V DC
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 6 kA
Rated Uninterrupted Current (I_u)	630 A
RoHS Date	NA
Short-Circuit Performance Level	D
Standards	IEC
Sub-type	T5
Suitable For	T5
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Fixed Circuit-Breakers Front
Test Voltage Max (U_{test})	3000 V
Test Voltage at Industrial Frequency for 1 Minute	3000 V
Version	F

Certificates and Declarations

ATEX Certificate	No certification needed
Data Sheet, Technical Information	1SDC210004D0203
Declaration of Conformity - CE	9AKK106713A5539
UL Certificate	No certification needed
VDE Certificate	No certification needed
Instructions and Manuals	1SDH000437R0001
Instructions and Manuals (Part 2)	ITSCE-RH0100001

Classifications

ETIM 7	EC000216 - Switch disconnecter
ETIM 8	EC000216 - Switch disconnecter
ETIM 9	EC000216 - Switch disconnecter (low voltage)
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.1 : 27371403

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

