

Profile Semi Deep Surface 16

Profile Semi Deep Surface 16 B/U4 2m anodised
0022597



Product features

- A semi deep 2000mm length anodised aluminium lighting profile that can be combined with slide (slick socket - easy assemble technology) opal diffuser (0022629) with a maximum LED strip width of 16mm. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



PRODUCT OVERVIEW

Product name	Profile Semi Deep Surface 16 B/U4 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278023
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288225975

DATA TABLE

General data

Product name	Profile Semi Deep Surface 16 B/U4 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278023
Warranty	3 years

Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	18.8
Nominal Product Height (mm)	18.6
Weight (kg)	0.39

Packaging

Single packaging type	Carton
Product EAN number	5410288225975
Packaging single length / height (cm)	200.0

Profile Semi Deep Surface 16

Profile Semi Deep Surface 16 B/U4 2m anodised
0022597

Packaging single width (cm)	1.6
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288225975
Units per outer package	50
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

TECHNICAL DRAWINGS

