

## Roughing cutter, HSSE Co 8

4 cutting edges, TiCN-coated


**ORION**<sup>®</sup>

### Application:

Roughing cutter for universal machining.

### Execution:

- HSSE Co 8
- fine roughing teeth
- centre cutting (over dia. 20 mm without centre cutting)
- TiCN coating for maximum service life requirements
- straight shank in accordance with DIN 1835 B



<b>Art. no.</b>	<b>15290 300</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	15290300
<b>Cutting material</b>	HSSE Co8
<b>Surface</b>	TiCN
<b>Type</b>	HR
<b>Number of cutting edges</b>	6 PCS
<b>Twist angle</b>	30°
<b>Edge protection chamfer length</b>	0.2 mm
<b>Tool holding device</b>	HB parallel shank
<b>Construction length</b>	Normal
<b>Cutting edge diameter</b>	30 mm
<b>Cutting edge length</b>	45 mm
<b>Length</b>	121 mm
<b>Shank diameter</b>	25 mm
<b>fz steel 1300</b>	0.14 mm
<b>Gross Weight</b>	0.486 kg
<b>Product Group</b>	106

### EAN

4039247094844