

DWLN steel boring bar, negative left

For facing and longitudinal turning with WN indexable insert

WIDIA 

Application:

For facing and longitudinal turning with WN indexable insert, 80°

Execution:

- Precision-manufactured steel boring bar, internal cooling, type W, pitch angle 95°, tip angle 80°, clearance angle 0°

Advantage:

- Three-edge geometry lowers cost per cutting edge
- Negative body geometry ensures good stability and absorption of force for large cutting depths



Art. no.	17684 016
Brand	WIDIA
Manufacturer Part Number	5696268
ISO name	A 25 R DWLN R/L 06
Min. bore diameter	32 mm
Shank diameter	25 mm
Length	200 mm
Programming size	17 mm
Suitable for indexable inserts	WN.. 0604..
Tool design	Left
Gross Weight	0.639 kg
Product Group	1XG

EAN

4050841471190