

Electronic 3-point internal micrometer set

Micromar 44 EWR



Application:

For measuring through-bores and for blind holes and short centring shoulders.

Version:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Interchangeable measuring heads
- Locking function
- Zero setting at any position
- mm/inch changeover
- ABS function
- preset function
- from Ø 40 mm, aluminium measuring head
- incl. setting rings

Delivery:

1 measuring element, measuring heads with setting rings, battery (1 x 3 V lithium type CR 2032)



Art. no.	31912 520
Min./max. length measuring range	12-20 mm
Measuring depth	64 mm
Error limit	4 µm
Data transmission type	multiCOM
Digit increment	0.001 mm
IP protection class	IP 52
Calibration Group	I
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863

EAN-Code

4059192011017