

Shelf boltless rack, single-row

Zinc-plated



Application:


Universal shelving system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools

Execution:

- Shelves height-adjustable in increments of 25 mm for variable adaptation to stored goods
- Shelves with a 50 mm hole grid to accommodate accessories, shelf edge height 40 mm
- For technical reasons, depth reinforcements are always zinc plated, even with coated frames
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm
- With dismantled or pre-assembled frame

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



| | |
|---|------------------|
| Art. no. | 50167 069 |
| Brand | META |
| Manufacturer Part Number | 20095031 |
| Height | 2500 mm |
| Length | 1006 mm |
| Depth | 536 mm |
| Nominal length | 1000 mm |
| Nominal depth | 500 mm |
| Design | Add-on shelving |
| Type of assembly | To insert |
| Surface | Zinc plated |
| Design of the frame | Disassembled |
| Grid dimension | 25 mm |
| Number of shelves | 6 PCS |
| Load-carrying capacity per shelf | 150 kg |
| Load-carrying capacity per field | 1650 kg |
| Number of frame | 1 PCS |
| Quality label | RAL-RG 614/1 |
| Made in | Germany |
| Gross Weight | 30.293 kg |
| Product Group | 508 |

EAN

4026212260328