

Pneumatic impact screwdriver E 18 P3

**MANNESMANN
DEMAG**

Execution:

- 4 throttle settings

Delivery:

Bracket, impact grease, oil bottle



Art. no.	75061 350
Brand	MANNESMANN DEMAG
Manufacturer Part Number	299 15325
Model	E 18 P3
Suitable for screw	M8 - M18
Max. tightening torque	400 Nm
Max. idle speed	6800 rpm
Air consumption	11.7 l/s
Tool holding device	1/2-inch external square
Hammer mechanism system	Twin hammer mechanism
Length	185 mm
Connection thread	IT 1/4 inch
Inner hose diameter	10 mm
Sound-pressure level	85 dB
Weight	2.4 kg
With right/left-hand rotation	Yes
Gross Weight	3.039 kg
Product Group	7AA

EAN

4251757300257