

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



tasker® TSK56 – 2x2,50mm² - Flat Audio Divisible Cable



A

B

CATEGORY Flat Cable (See Audio Catalogue)

A: Red and Black Soft **PVC** Sheath.
 Outer cable dimension 3,70x7,40 mm (±0,10) mm.

B: Both conductors in CCA - Formation with 0,20 mm wires.
 Nominal cross section 2x2,50 mm².

CUSTOM This product is also available in **L.S.Z.H., PE, PUR.**

Cable Properties

Conductor Resistance	6 Ω/Km ± 5%
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 16.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		