

## CUBE20S COUNTER MODULE

1 x 32 Bit bis 400Khz+1DO


Counter module

1 x 32 Bit

max. 400 kHz

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



### Internal communication

Module Supply	24 V DC (20.4...28.8 V DC)
Current consumption	max. 75 mA

### General data

Protection	IP20
Connection	Spring clamp plug-in terminals: max. 1.5 mm <sup>2</sup> (AWG 16)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

### Counter

Counter input	1
Counter frequency	max. 400 kHz
Counter depth	32 Bit (31 Bit + sign)

### Diagnostic

Communication status	via LED
Diagnostic via LED	per module
Diagnostic via BUS	per module
Monitoring - under voltage	yes
Monitoring - no voltage	no
Short circuit and overload	yes

### Commercial data

country of origin	TH
customs tariff number	90291000
minimum order quantity	1