


M12 MALE ON TOP OF MSUD VALVE PLUG FORM BI 11MM


Form BI (11 mm) – M12, connector top entry
LED and suppression
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Form

42021

Technical Data

Operating voltage	24 V AC $\pm 20\%$ / DC $\pm 25\%$
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Switch off peak	max. 55 V
Switching current	max. 15 mA
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	M3 (recommended torque 0.4 Nm)

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	CZ
customs tariff number	85369010

minimum order quantity

1