

PRODUCT-DETAILS

SP25/M25/B

M25 SWIVEL FITTING FOR SP25



General Information

Extended Product Type	SP25/M25/B
Product ID	7TCA296020R0198
EAN	5020963000089
Catalog Description	M25 SWIVEL FITTING FOR SP25
Long Description	Nickel Plated Brass Straight Fitting with Swivel External Thread, Nominal Conduit Size 25 Millimeters, Metric Thread Size M25

Ordering

EAN	5020963000089
Customs Tariff Number	7412200025

Dimensions

Product Net Weight	.145 lb 65.76 g
--------------------	--------------------

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	1.6 in 41 mm
Package Level 1 Height	1.4 in

	36 mm
Package Level 1 Depth / Length	1.5 in 38 mm
Package Level 2 Units	150 piece
Package Level 2 Width	14 in 356 mm
Package Level 2 Height	14 in 356 mm
Package Level 2 Depth / Length	6 in 152 mm

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M25 Thread
Color	Metallic
Material	Brass
Number of Batteries	0
Product Name	BRASS FITTING FOR CONDUIT
Product Type	Conduit Fitting with Metric Threads
Size	3/4 Inch
Surface Finishing	Nickel Plated
UPC	786210249117

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP25/M25/B
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP25/M25/B

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

